

## Determine the Wavelength of Sodium Light by Fresne



We are an acclaimed supplier of a qualitative array of **Determine the Wavelength Of Sodium Light By Fresne** to our highly esteemed clients. It is a testing equipment made up of high-grade raw material and advanced machinery at our unit in sync with the set industrial norms and standards. **Determine the Wavelength of Sodium Light By Fresne** stands high on quality, durability, accuracy and performance, hence making us credible for our clients. We strive to deliver it within a set time frame.

### **Objective:**

Determine the Wavelength of Sodium Light

### **Setup consists of:**

- Optical Bench 1.5mtrs with Bi-Prism Assembly
- Biprism
- Single Slit
- Convex Lens 10cm FL
- Sodium Vapour Lamp 35 Watt fitted in Box with Transformer